

LED LENSER® i6R

The LED Lenser i6R is one of the first pen lights available with re-charging option and is perfect for penetrating less accessible locations that need plenty of light. Its longer barrel is ideal for illuminating narrow or confined spaces in workshops, factories and garages. The precise internal reflector lens is fitted with a CREE® Power LED Light Chip, which employs the patented Advanced Focus System to shine bright, homogenous white light all the way from flood to spot beam, and is capable of picking out a component or blemish some distance away with pinpoint accuracy. There is a choice of Power or Low Power light settings, providing everything from high-intensity illumination down to a softer light useful for reading maps or viewing diagrams. Single-hand Speed Focus and an easy-grip metal body make handling comfortable for extended use. Performance optimised to provide 120 lumens for up to 4 hours, the i6R is a great choice for engineers and construction personnel who need sustained bright white light.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Stylish rechargeable pen-light torch with contact charging docking station
- CREE® Power LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System (AFS). Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Speed Focus® (one-handed spot-to-flood beam)
- Dynamic Switch
- Power and Low Power light modes
- Charging docking station with charging status indicator
- USB connection for recharging
- Pocket Clip
- Water-resistant (IPX4)
- Robust metal housing

Technical Information	Power	Low Power
Lumens	120	10
Beam Distance (meters)	100	30
Run Time (hours)	4	25
Size:	170x19mm Ø	
Weight:	82g	
Batteries:	3 x AAA NiMH	
Supplied with: USB Charging Cable, Charging Docking Station, Pouch, Rechargeable Battery Set (3 x AAA NiMH)		

* Also compatible with AAA Alkaline batteries (not supplied)

Code	Description	Unit Colour	Packaging	Barcode
5606R	i6R	Black	Box	4029113560634
RRP ex.vat £41.63 / incl.vat £49.95				