

Datasheet

RS Pro 4 Pole Non-Fused Switch Disconnecter, 40 A, IP54

RS Stock No: **773-8033**



Product Details

RS Pro 4-pole non-fused switch disconnecter has a current rating of 40 A. It is constructed from flame retardant ABS for long life durability. This IP54 rated unit is easy to access and has interlocking lid that ensures removal in the off position. It is suitable for use with low voltage switchgear such as power distribution, load isolation and motor start/stop. The switch disconnecter meets EN60947 standards.

Features and Benefits

- Interlocking lid ensures removal in the OFF position only
- Easy access and switch removal
- Padlockable handles
- Flame retardant material

**Specifications:**

Accepts Padlocks	Yes
Auxiliary Contacts Available	Yes
Depth	90 mm
Electrical Phase	3
Handle Colour	Red
IP Rating	IP54
Length	220 mm
Maximum Current	40 A
Maximum Operating Temperature	+40°C
Minimum Operating Temperature	-25°C
Mounting Type	Panel Mount
Number of Poles	4
Switch Rating	30 kA
Voltage Rating	690 V ac
Width	145 mm
Cable Capacity	10 mm ²
Material	ABS Plastic Enclosure
Standards Met	EN 60947
Tightening Torque	1.7 Nm