





NO	DESCRIPTION	DATE
①	PART ② MODIFICATION	03.25.99'
②	BACKGROUND FORMAT UPDATED	12.23.04'
③	BACKGROUND FORMAT UPDATED	04.12.11'
④	DEL PROOF VOLTAGE WORKING VOLTAGE → VOLTAGE RATING	06.11.15'



STRIPPING DIMENSION

1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-2.5 GHz
1.2 NOMINAL IMPEDANCE: 50 OHM
1.3 VOLTAGE RATING: 335 VOLTS MAX. 

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
2.2 CENTER CONTACT: BRASS PER JIS-C3604
2.3 CRIMP FERRULE: BRASS PER JIS-C2700

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.**

4.0 MECHANICAL

- 4.1 FOR USE WITH RG58U OR SIMILAR STYLE CABLE
4.2 CABLE ATTACHMENT: OUTER: CRIMP, INNER: SOLDER /CRIMP
4.3 CRIMP SIZE REQUIRED: CONTACT: 1.8(.071) HEX. CRIMP TOOL
FERRULE: 5.5(.216) HEX. CRIMP TOOL

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -40° C TO +60° C**

5	CRIMP FERRULE	BRASS	1	NICKEL
4	CENTER CONTACT	BRASS	1	GOLD
3	INSULATION	POM	1	NONE
2	BODY	BRASS	1	NICKEL 100 μ " MIN.
1	WASHER	BRASS	1	NICKEL
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH



APPROVED

by DATE:

DESCRIPTION			MINI-UHF STRAIGHT JACK CRIMP												
製圖	DRAWN	TOLERANCE		品名		12-01-1		D.G.N		58U		日期	DATE	版次	REV.
	Kristina	.X	±0.2	TITLE		\R0HS COMPLIANT		(50Ω)					01.13.93'		A-4
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.	12-0004								
	Arc				mm(in)										
認定	APPROVAL	.XXX	±0.05	比例	SCALE										
	Angela				ANGLE										