

General Information

Extended Product Type:	332-P6
Product ID:	2CMA193515R1000
EAN:	7392696935159
Catalog Description:	Plug, 6h, 32A, IP44, 3P+E
Long Description:	Plug, earthing sleeve position 6h, rated current 32A, IP44 splashproof, 3-poles+earth, 50 - 60 Hertz, color code red

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Plugs

Ordering

EAN:	7392696935159
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	90 mm
Product Net Height:	90 mm
Product Net Length:	162 mm
Product Net Weight:	0.215 kg

Container Information

Package Level 1 Width:	180 mm
Package Level 1 Length:	155 mm
Package Level 1 Height:	378 mm
Package Level 1 Gross Weight:	0.215 kg
Package Level 1 EAN:	7392696935159
Package Level 1 Units:	10 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700022

Additional Information

Additional Information:	Cable entry, compression gland
Cable Cross-Section:	2.5 ... 6 mm ²
Color:	Red
Degree of Protection:	IP44
Enclosure Material:	Polyamide
Frequency (f):	60 Hz
Function:	Plug
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#332-P6
Number of Poles:	4
Object Classification Code:	2CMT005069
Product Main Type:	P
Product Name:	Industrial Plug
Protection Type:	Splashproof
Rated Current (I _n):	32 A
Rated Voltage (U _r):	380 ... 415 V
RoHS Date:	2009-1
Standards:	IEC 60309-1,-2
Suitable For:	Plugs
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer: 2416174

UNSPSC: 39120000

