

# PROSAFE INDUSTRIAL USB RECHARGEABLE HEADLIGHT

PS-H10R



**3-45**  
HOURS  
RUNTIME

**280**  
METRE  
BEAM RANGE

**1100**  
LUMENS  
OUTPUT

**IPX4**  
WATER  
RESISTANCE

- » 1100 Lumen White XM-L2 CREE LED
- » Multi-faceted deep reflector
- » Impact resistant to 1m
- » 3 stage dimming electronic switch
- » 8Hz & 2Hz strobe and SOS functions
- » 90° Rotational head
- » White rear battery pack light
- » Rubberised non-slip headbands
- » 3M reflective strips for greater visibility
- » Micro USB charging cable (included)
- » Battery level indicator lights

**BATTERY** 1 x 3.7v 2600 mAh 18650 Li-ion Battery (included)  
**WEIGHT** 229g (with battery)  
**DIMENSION** Headlight: 51 x 69 x 45mm - Battery Pack: 50 x 83 x 45mm

LIGHT BY  
**CREE**   
 LEDS

**USB**  
 CHARGING



MICRO-USB CABLE (INC)



WHITE BATTERY PACK LIGHT



RUBBER MICRO SWITCH



HELMET MOUNTABLE