

Crimping pliers - CRIMPFOX-RCT 70-1 - 1212732

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for uninsulated tube lugs, 10 - 70 mm², indent crimp

Why buy this product

- Ergonomically designed handles ensure an optimum grip and help avoid fatigue when working.
- Crimping pliers for uninsulated tube lugs
- Compact and lightweight design
- Unlockable pressure lock



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 857918
Weight per Piece (excluding packing)	3073.3 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	492 mm
Height	80 mm
Width (a)	44 mm

General

Color	black
Compression	Indent crimp
Type of contact	CU conduit lugs
Designation	Crimping position 1
Max. cross section	10 mm ²
AWG max	8

Crimping pliers - CRIMPFOX-RCT 70-1 - 1212732

Technical data

General

Designation	Crimping position 2
Max. cross section	16 mm ²
AWG max	6
Designation	Crimping position 3
Max. cross section	25 mm ²
AWG max	3
Die station	Crimping position 4
Max. cross section	35 mm ²
AWG max	2
Die station	Crimping position 5
Max. cross section	50 mm ²
AWG max	0
Die station	Crimping position 6
Max. cross section	70 mm ²
AWG max	00

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518