

LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	ECR-06-013423	14JUN06	JMS	FWK

NOTES:

- 1

PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3

Au PLATING
- 4

Ni PLATING
- 5

ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:DC - 2 GHz

NOMINAL IMPEDANCE:75 Ohm

INSULATION RESISTANCE:5000 MOhm

WORKING VOLTAGE:500 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:1500 Volts RMS Max

CONTACT RESISTANCE:1.50 mOhm Max

CENTRE CONTACT:0.20 mOhm Max

OUTER CONTACT:N/A

VSWR @ xGHz:N/A

INSERTION LOSS xdb:N/A
- 6

MECHANICAL CHARATERISTICS

COUPLING RETENTION FORCE:N/A

CABLE RETENETION FORCE:N/A

MOUNT NUT RECOMMENDED TORQUE:4N



DURABILITY:500 Cycles Min
- 7

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:-65 to +165 DegC
- 8

FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
- 9

ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



		2	2	PTFE	INSULATION	6
		1	1	BRASS	CONTACT	5
		1	1	BRASS	BODY	4
		1	1	BRASS	WASHER	3
		1	1	BRASS	LOCKWASHER	2
		1	1	BRASS	HEX NUT	1
		6--0	1--0	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY				PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J.SANDWELL	14JUN06	tyco Tyco Electronics Corporation	
		CHK	S.PARLOW	14JUN06		
		APVD	F.WHEELER-KING	14JUN06	Bideford EX39 4HE	
		PRODUCT SPEC			NAME	
					BNC BULKHEAD ADAPTOR J-J 75 OHM	
		APPLICATION SPEC				
		WEIGHT				
		CUSTOMER DRAWING				
					SIZE	CAGE CODE
					A3	00779
					DRAWING NO	
					C-1478047	
					RESTRICTED TO	
					-	
					SCALE	NTS
					SHEET	1 OF 1
					REV	B