

Housing - HC-D 15-SML-52/M2PG16 - 1772395

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Box mounting base, with single locking latch, height 52 mm, with screw connection, 2x Pg16

The illustration shows version, HC-D 15-SML-52/M 1 PG 16



Key commercial data

Packing unit	10 pc
GTIN	 4 017918 037062
Weight per Piece (excluding packing)	236.47 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Height	52 mm
Width	50 mm
Length	93 mm
Wrench size, union nut	22 mm
External cable diameter	7.5 mm ... 15 mm (Cable 1)
	7.5 mm ... 15 mm (Cable 2)

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-D15, A10
Type	D15
Housing type	Box mounting bases

Housing - HC-D 15-SML-52/M2PG16 - 1772395

Technical data

General

Locking type	With single locking latch
No. of cable outlets	2
Cable exit	Lateral
Screw connection	with
Type of the screw connection	2x Pg16
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Cable gland material	Nickel-plated brass
Cable seal material	NBR
Material lock	Steel, galvanized

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC / GL

Housing - HC-D 15-SML-52/M2PG16 - 1772395

Approvals

Ex Approvals

Approvals submitted

Approval details

EAC

GL

Drawings

Dimensioned drawing

