

Datasheet

RS Pro 3A Axial FF Non-Resettable Wire Ended Fuse, 125 V ac/dc

RS Stock No: **764-9488**



Product Details

RS Pro axial non-resettable fuse withstands currents up to 3 A. This wire-ended fuse offers FF speed with a voltage rating of 125 V ac/dc. It has epoxy-coated body for added durability. The very fast acting fuse forms a convenient and reliable solution to a vast array of application requirements.

Features and Benefits

- FF speed fuse
- Non-resettable
- Axial
- Wire-ended

**Specifications:**

| | |
|---|-------------------------------------|
| Body Diameter | 2.65 mm |
| Body Height | 7.1 mm |
| Body Material | Epoxy Coated |
| Breaking Capacity (at Maximum Voltage Rating) | 300 A at 125 V dc, 50 A at 125 V ac |
| Current Rating | 3 A |
| Fuse Speed | FF |
| Lead Orientation | Axial |
| Maximum Operating Temperature | +125°C |
| Minimum Operating Temperature | -55°C |
| Voltage Rating | 125 V ac/dc |
| Voltage Rating | 125 V ac/dc |
| Wire Diameter | 0.65 mm |
| Wire Length | 28 mm |
| Fuse Type | Very Fast Acting |
| Nominal Resistance | 0.024 Ω |
| Standards Met | TUV, CCC, PSE, RoHS |
| | |