


LOC		DIST		P		F		ZONE		LTR		DESCRIPTION		DATE	APPD
G		14								C		REVISED & REDRAWN PER 0720-0120-93		8/4/93	✓ AJK



METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	UL E13288 Listed
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
2/0 AWG SOLID OR STRANDED	NOT APPLICABLE

△ STAMP AMP 2/OW* 125 APPROX AS SHOWN

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

CIRCULAR MIL AREA:
60.6-76.3mm² [119,500-150,500] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± 0.20 [0.008]
3 PLC DEC ± -
ANGLES ± -
MATERIAL
COPPER PER ASTM B-152
ANNEALED

FINISH
TIN PLATE
0.00254 [0.000100] MIN
THK PER MIL-T-10727

DR 8/4/93
DK SCHRUM
CHK 8/5/93
AJ KAUFMAN

APPD 8/5/93
RE ROSER
APPD 8/5/93
JL MECKLEY
PRODUCT SPEC

APPLICATION SPEC
-
WEIGHT -

AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME
**TERMINAL, RING TONGUE,
SOLISTRAND™**

SIZE
C 00779
CAGE CODE
DRAWING NO
C-322224

SCALE 2:1
SHEET 1 OF 1