

Control and signalling units Ø 22

Spare parts and accessories

PVC legend plates 30 x 40 mm

"Start" functions : white characters on black background. "Stop" functions : white characters on red background.

Text	Reference	Text	Reference	Text	Reference
Text in English					
Auto	ZB2-BY2115	Hoist up	ZB2-BY2341	Raise	ZB2-BY2335
Auto-Hand	ZB2-BY2364	Inch	ZB2-BY2321	Reset (rouge)	ZB2-BY2323
Auto-O-Hand	ZB2-BY2385	Jog-For	ZB2-BY2381	Reset (noire)	ZB2-BY2322
Bridge forward	ZB2-BY2343	Jog-Rev	ZB2-BY2380	Reverse	ZB2-BY2306
Bridge reverse	ZB2-BY2344	Jog-Run	ZB2-BY2365	Right	ZB2-BY2309
Close	ZB2-BY2314	Left	ZB2-BY2310	Run	ZB2-BY2334
Down	ZB2-BY2308	Low	ZB2-BY2336	Slow	ZB2-BY2327
Emergency stop	ZB2-BY2330	Lower	ZB2-BY2337	Start	ZB2-BY2303
Fast	ZB2-BY2328	Man-Auto	ZB2-BY2372	Start-Stop	ZB2-BY2362
For-Rev	ZB2-BY2371	Off	ZB2-BY2312	Stop	ZB2-BY2304
For-O-Rev	ZB2-BY2384	Off-On	ZB2-BY2367	Trolley left	ZB2-BY2346
Forward	ZB2-BY2305	On	ZB2-BY2311	Trolley right	ZB2-BY2345
Hand	ZB2-BY2316	Open	ZB2-BY2313	Up	ZB2-BY2307
Hand-Off-Auto	ZB2-BY2387	Open-Close	ZB2-BY2376	Up-Down	ZB2-BY2370
High	ZB2-BY2338	Open-O-Close	ZB2-BY2388	Up-O-Down	ZB2-BY2389
High-Low	ZB2-BY2369	Out	ZB2-BY2339		
Hoist down	ZB2-BY2342	Power on	ZB2-BY2326		

Text in German					
Ab	ZB2-BY2208	Auto-Hand	ZB2-BY2364	Links	ZB2-BY2210
Auf	ZB2-BY2207	Auto-O-Hand	ZB2-BY2385	Rechts	ZB2-BY2209
Aus	ZB2-BY2204	Ein	ZB2-BY2203	Vorwärt	ZB2-BY2205
Auto	ZB2-BY2115	Hand	ZB2-BY2316	Rückwärt	ZB2-BY2206


Text in Italian					
Aggancio	ZB2-BY2631	Avanti-O-Indietro	ZB2-BY2684	Inser-Disinser	ZB2-BY2667
Apertura	ZB2-BY2613	Chiusura	ZB2-BY2614	In Servizio	ZB2-BY2611
Arresto	ZB2-BY2604	Destra	ZB2-BY2609	Lento	ZB2-BY2627
Arresto generale	ZB2-BY2629	Discesa	ZB2-BY2608	Marcia	ZB2-BY2603
Arresto-Marcia	ZB2-BY2666	Disinserito	ZB2-BY2632	Riarmo	ZB2-BY2623
Arresto riarmo	ZB2-BY2633	Emergenza	ZB2-BY2630	Salita	ZB2-BY2607
Auto-Man	ZB2-BY2664	Fuori-In	ZB2-BY2663	Sinistra	ZB2-BY2610
Auto-O-Man	ZB2-BY2685	Fuori Servizio	ZB2-BY2612	Sotto tensione	ZB2-BY2626
Avanti	ZB2-BY2605	Indietro	ZB2-BY2606	Veloce	ZB2-BY2628

Text in Spanish					
Marcha	ZB2-BY2403	Parada	ZB2-BY2404		

Text in Dutch					
Auto	ZB2-BY2115	Hand	ZB2-BY2316	Rechts	ZB2-BY2209
Auto-Hand	ZB2-BY2364	In	ZB2-BY2503	Uit	ZB2-BY2504
Auto-O-Hand	ZB2-BY2385	Links	ZB2-BY2210		

Texts in Danish					
Abne	ZB2-BY28131	Ind	ZB2-BY28111	Op	ZB2-BY28071
Aut-Man	ZB2-BY28641	Lukke	ZB2-BY28141	Tilbage	ZB2-BY28061
Aut-O-Man	ZB2-BY28851	Man-Aut	ZB2-BY28821	Ud	ZB2-BY28121
Down	ZB2-BY28142	Man-O-Aut	ZB2-BY28901	Ude-Inde	ZB2-BY28671
Drift	ZB2-BY28134	Ned	ZB2-BY28081	Up	ZB2-BY28143
Frem	ZB2-BY28051	Nødstop	ZB2-BY28301	Vip	ZB2-BY28201

Special texts	Reference	Weight kg
Please state the exact wording when ordering	one off	ZB2-BY2002 0,001
	2 to 10 ident.	ZB2-BY2002-02 0,001
	more than 10	ZB2-BY2002-11 0,001
2 lines 11 characters maximum per line	one off	ZB2-BY2004 0,001
	2 to 10 ident.	ZB2-BY2004-02 0,001
	more than 10	ZB2-BY2004-11 0,001
Black background, white characters	one off	ZB2-BY4001 0,001
	2 to 10 ident.	ZB2-BY4001-02 0,001
	more than 10	ZB2-BY4001-11 0,001
Red background, white characters	one off	ZB2-BY4005 0,001
	2 to 10 ident.	ZB2-BY4005-02 0,001
	more than 10	ZB2-BY4005-11 0,001
White background, black characters	one off	ZB2-BY4005 0,001
	2 to 10 ident.	ZB2-BY4005-02 0,001
	more than 10	ZB2-BY4005-11 0,001
Yellow background, black characters	one off	ZB2-BY4005 0,001
	2 to 10 ident.	ZB2-BY4005-02 0,001
	more than 10	ZB2-BY4005-11 0,001



ZB2-BY...
Weight Kg 0,001