

LED LENSER® M7R – Rechargeable 2014

This handsome multi-function torch has up to 10 micro-chip controlled options and an intelligent, environment-friendly recharge capability. Made from German-engineered anodised aluminium for durable, long-term use, it features internal gold-plated contacts for corrosion-resistance and superior conductivity. Using the patented Advanced Focus System it projects universally consistent light from flood to spot, with single-handed Speed Focus to quickly zoom between them. Comprehensive Smart Light Technology offers the user two Energy Modes to regulate power usage and eight Light Options: Power; Low Power; Blink; Boost; Dim; Defence Strobe; Morse and SOS - across three pre-set Light Programmes. Inside a formidable new-generation CREE LED sends intense white light up to 280 metres at a maximum 400 lumens and 40 hours burn time. With its wide-angle reflector lens it will project high-intensity white light across an exceptionally broad area. The rechargeable nature of this torch eliminates the need for disposable batteries and thus helps make it that little bit more sustainable and easier on the planet. It uses a single rechargeable Lithium Ion battery and Low Battery Message System to indicate when charging is necessary. The 'stow-and-go' Floating Charge System, one of the most effective contact chargers in the world, conveniently allows the battery to be charged without removing it from the housing. The M7R torch is supplied in a hard case for protective storage that also contains a rechargeable battery, mains charger, USB cable, wall-mount, wrist strap and 360° belt clip.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class- leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability second to none.

- Rechargeable medium sized torch packed full of the latest illumination technology
- Energy efficient CREE Power+ LED Light Chip
- Increased light output from wide-angle, calibrated reflector lens
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Smart Light Technology™. Micro-chip controlled multi-option technology with two energy usage modes, three pre-set light programs utilising eight light options (Morse, Dim, Boost, Power, Low Power, Blink, SOS, Defence Strobe)
- Floating Charge System™ – effortless contact recharging
- Dynamic Switch™ - Reactive, single switch control
- Speed Focus™ enables smooth single-handed beam focusing
- Fast Lock™ - locks the beam position and prevents accidental refocusing.
- 360° Belt Clip enables hands-free directional illumination
- Low Battery indicator
- Robust, yet lightweight aircraft-grade aluminium housing
- User-friendly modular design
- Corrosion resistant gold plated contacts for better conductivity
- Water and dust resistant (IPX54)

Technical Information

Size: 153 x 38mm Ø

Power: 400 lumens max

Run Time: up to 40 hours

Beam Distance: up to 280m

Weight: 200grams

Supplied with : Hard Case, Mains Charger, USB cable, Wall Mount, Wrist-strap, 360° Belt Clip and Rechargeable Battery (1xLi-ion 3.7v)

Code	Colour	Packaging	Barcode
8407R	Black	Hard Case	4029113830737