



ENGLISH

Datasheet

Stock No: 410-145

# RS Pro Right Angle Switchable IP66, IP67 Interlocked Socket 2P+E, Earthing Position 6h, 16A, 250 V



## Product Details

### Horizontal style with switch

These RS Brand surface mounted outlet sockets feature hard plastic housing and a socket cover. They are designed for industrial use, but are also suitable for commercial environments.

Designed with safety in mind, this range also features a mechanical interlock that prevents the switch from closing if the plug is not inserted, the extraction of the plug if the switch is closed, and the opening of the socket outlet cover if the switch is closed.

These outlets are available as protected to either IP44 (splash proof) or IP67 (watertight.)



Locking switches

## Specifications

Plug/Socket	Socket
Pole Format	2P+E
Switchable	Yes
Colour	Blue
IP Rating	IP66, IP67
Voltage Rating	250 V
Current Rating	16A
Body Orientation	Right Angle
Dimensions	136 x 125 x 202mm
Earthing Position	6h
Body Material	Polymer
Depth	202mm
Length	136mm
Width	125mm