

GC420™ Desktop Printer

Model	Part Number	Description All GC420 printers have EPL and ZPL firmware (SGD, XML, Unicode), Direct Thermal and Thermal Transfer print modes. Power Supply with UK and Euro power cord included. All GC420 configurations include 8MB SDRAM (2MB user available), 8MB Flash (6MB user available)	CONFIGURATION								
			Max. Print Speed mm/s (ips)	Maximum Print Width (mm)	Resolution 8 dots/mm (203 dpi)	Print Mode		connectivity: Serial, Parallel & USB	connectivity: USB, Ethernet	Media Handling	
						Direct Thermal	Thermal Transfer			Tear	Peel
GC420d	GC420-200520-000	GC420, Direct Thermal, 203 dpi, Serial, Parallel & USB	102 (4)	104	✓	✓		✓		✓	
	GC420-200420-000	GC420, Direct Thermal, 203 dpi, USB, 10/100 Ethernet	102 (4)	104	✓	✓			✓	✓	
	GC420-200521-000	GC420, Direct Thermal, 203 dpi, Serial, Parallel & USB, Peel	102 (4)	104	✓	✓		✓			✓
GC420t	GC420-100520-000	GC420, Thermal Transfer, 203 dpi, Serial, Parallel & USB	102 (4)	104	✓		✓	✓		✓	
	GC420-100420-000	GC420, Thermal Transfer, 203 dpi, USB, 10/100 Ethernet	102 (4)	104	✓	✓			✓	✓	
	GC420-100521-000	GC420, Thermal Transfer, 203 dpi, Serial, Parallel & USB, Peel	102 (4)	104	✓		✓	✓			✓

GC420™ Kits

	Part Number	Description
Connectivity	105850-001	Parallel Interface Cable 6' (Centronics)
	105850-006	USB Interface Cable 6' (A to B)
	G105850-003	Serial Interface Cable - 6' (DB-9 to DB-9)
	G105950-054	Serial Interface Cable 6' (DB-9 to DB-9) Null Modem
	P1031031	External ZebraNet 10/100 Print Server v2 ¹
Media Handling	105810-003	Media Adpater Guide 4"
Other	ZKDU-001-00	ZKDU, Zebra Keyboard Display Unit
	105950-035	Printhead Cleaning Pens x 12
	G105910-048	Printhead Assembly, Direct Thermal 203 dpi
	G105910-053	Printhead Assembly, Thermal Transfer 203 dpi
	105910-001	Platen Kit, GC420d (set of 3)
	105910-055	Platen Kit, GC420t (set of 3)
	105950-050	Shipping Pack
	P1027135-048	Ribbon Core, 4" Thermal Transfer (set of 50)

1. Requires Centronics parallel port.