

General Information

Extended Product Type:	BJMI8-4
Product ID:	1SNA176671R0000
EAN:	3472591766714
Catalog Description:	BJMI8-4 POLES Jumper Bars
Long Description:	BJMI8-4 - Jumper Bars - 4 poles - - 8mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

EAN:	3472591766714
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	10.00 g
----------------------------	---------

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	155 mm
Package Level 1 Height:	5 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0,1 kg
Package Level 1 EAN:	3472591766714
Package Level 2 Units:	500 piece

Additional Information

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Type:	Fractionnable model, composed of captive screws on a jumper bar, with IP20 protection touchproof. This accessory can be used for connecting consecutive blocks only.
Product Main Type:	BJMI
Product Name:	Jumper Bar
Rated Current (I_n):	Main Circuit 41 A
Spacing:	8 mm
Sub-Function:	Assembled jumper bar

Sub-Function 2:

Screw

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225001C1009

GOST Certificate: 1SND161005A1104

RoHS Information: 1SND230492F0201

Classifications

ETIM 4.0: EC000489 - Cross-connector for terminal block

ETIM 5.0: EC000489 - Cross-connector for terminal block

Object Classification Code: X

