



■ MS10

➔ Insulated half-round straight long nose pliers

▶ STANDARD :

EN 60900 / IEC60900

ISO 5743

ISO 5744

ISO 5745



Ref.	Cutting capacity	Length	Weight
MS10 170	Medium-hard steel wire 160 kg/mm ² : ø 1,6 mm	170 mm (6,5")	175 g
MS10 205	Medium-hard steel wire 160 kg/mm ² : ø 1,6 mm	205 mm (8")	240 g

Document not contractually binding, errors and omissions excepted.