



Save as PDF



**3715 LED Zone 0 Flashlight**



Peli leads the way yet again with its new right angle light. Featuring downcast LEDs for illuminating your path, the new 3715Z0 LED light also features 174 lumens (high) and 95 lumens (low), and a signaling mode.

Another first is a built in battery life indicator so you will know your light's battery level before you go in.

Compact, rugged, and lightweight, the 3715Z0 LED light contains the latest technology, Peli's legendary build quality and [Peli's Legendary Guarantee of Excellence](#).

The new 3715Z0 LED - Now you can WATCH YOUR STEP.



**3715 LED Zone 0 Flashlight  
ANSI FL1 Specifications**

<b>LIGHT SOURCE.</b>	High	
	LED	
<b>BATTERIES</b>	4 AA Alkaline (Not included)	
<b>CHARGE TIME</b>	No	
<b>VOLTAGE</b>	6	
<b>LENGTH</b>	13.6 cm (5.36")	
<b>WEIGHT W/ BATTERIES</b>	0.17 kg (6 oz.)	
<b>WEIGHT W/O BATTERIES</b>	0.31 kg (11 oz.)	

**LIGHT OUTPUT**  
**RUNTIME (hours/min)**  
**BEAM DISTANCE (meters)**  
**PEAK BEAM INTENSITY (candela)**

FL1 STANDARD	High	Low
	4h 45m	
	278m	175 m.
	19389cd	8051cd

**Materials**

Body	Lens	Shroud	Switch Type
ABS	Polycarbonate	ABS	4 Modes - High, Low, Down-cast only & Flashing
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
Xenoy polymer		Buna-N	

**Configuration**

Cat. #	Description
3715Z0	3715 LED Zone 0 Flashlight

**3715 LED Zone 0 Flashlight Accessories**

No accessories are currently available for this product

**Approvals**

CE Ex - II 1G Ex ia IIC T4 Ga  
Certificate: TRAC12ATEX0018X