



Industrial Connector Solutions

- Home
- About us
- Applications
- Products
- Technical Data
- Contact us
- News

New User? Sign Up
Forgot Password

Email ID

Password

LOGIN

Home > Product Finder > eCatalog > JBX Push Pull Unsealed IP40

CIRCULAR RECTANGULAR PUSH PULL CABLE ASSEMBLIES OTHER PRODUCTS

[Industrial](#) > [Push Pull](#) > [JBX Push Pull Unsealed IP40](#) > JBX DOUBLE NUT RECEPTACLE SZ0 2 POSITION FEMALE CRIMP

JBX DOUBLE NUT RECEPTACLE SZ0 2 POSITION FEMALE CRIMP

Quick Search

Product or item # ok

[Advanced Search](#)



JBXEA0G02FCSDS
JBX DOUBLE NUT RECEPTACLE SZ0 2 POSITION FEMALE CRIMP
Characteristics, 3D model and drawing

Select P/N



Share with a friend

P/N Summary

You have selected 0 P/N

[Technical Info](#) [3D / Drawing](#) [Associated Products](#) [Equivalent Products](#) [Check Availability](#)

Product Description - JBX DOUBLE NUT RECEPTACLE SZ0 2 POSITION FEMALE CRIMP

Navigation Tracing

Categories

[JBX Push Pull Unsealed IP40](#)

Items

[JBXEA0G02FCSDS : JBX DOUBLE NUT RECEPTACLE SZ0 2 POSITION FEMALE CRIMP](#)

Code :	JBXEA0G02FCSDS
Number of contacts :	2
Layout with Protective Earth cavity :	No
Current (A) :	10
Voltage (V) :	600
Contact termination :	CRIMP SUPPLY
Size of contact (mm) :	0,9
Wire acceptance maxi (AWG) :	20
Contacts delivered with connector ? :	Yes
Contact Plating :	GOLD
Sealing :	IP64
Type of connector :	PLUG
Contact gender :	Female
Operating temperature mini (°C) :	-55
Operating temperature max (°C) :	155
Flammability :	UL94 V0
Durability (cycles mating-unmating) :	1000
Vibrations :	> 10 to 2000Hz y = 15g per Mil-Std1344A, Method 2005.
Thermal chocs :	50g, duration 6ms, per Mil-Std-1344A, method 2004.1
Width (mm) :	12
Length (mm) :	19
Panel thickness (mm) :	6,7

