

Datasheet

RS Pro On/Off Temperature Controller, 77 x 35mm, Digital Input, 24 V ac/dc Supply

RS Stock No: 875-1295



Product Details

RS Pro on/off temperature controller of size 77 x 35 mm, comes with digital input and has a supply voltage of 24 V ac/dc. Digital potentiometer control panel for V/F speed controller is designed for controlling the speed and direction of the motor as a control panel for V/F speed controllers in industry. They can be used in many applications with their easy use and operation with their ramp properties.

Features and Benefits

- 4 digits display
- Easily adjustable set value from front panel
- Configurable display scale between -1999 and 9999
- Adjustable decimal point
- Set value low and high limit boundaries
- Adjustable ramp up and ramp down time
- Forward, reverse direction outputs and error inputs for V/F speed controller
- Password protection for programming and adjustment sections

**Specifications:**

Input Type	Digital
IP Rating	NEMA 4X
Maximum Operating Temperature	+50°C
Minimum Operating Temperature	0°C
Mounting Type	1/16 DIN Rail
Number of Inputs	1
Number of Outputs	1
Output Type	Current
Panel Depth	62.5 mm
Size	77 X 35 mm
Supply Voltage	24 V ac/dc
Termination Type	Screw
Panel Cut Out Size	71 x 29 mm