

## CTM30M4



Article Number: 151-30603

Cable Tie Mount, 0.2" Hole Dia., 0.31" Max Tie Width, PA66, Black, 1000/pkg



Download spec sheet

### Base Data

<b>Local Order Number</b>	CTM30M4
<b>Type</b>	CTM3
<b>Color</b>	Black (BK)
<b>Features and Benefits</b>	<ul style="list-style-type: none"> <li>• Designed for use with 18 through 120 pound cable ties to provide stability when securing bundles.</li> <li>• Secures with a single screw providing quick installation.</li> </ul>
<b>Product Description</b>	HellermannTyton cable tie mounts are designed for use with 18 through 120 pound cable ties to provide stability when securing bundles. The mounts are installed quick and easy by securing a single screw.
<b>Fixation Method (FF)</b>	Screw Mounting and Rivet
<b>Short Description</b>	Cable Tie Mount, 0.2" Hole Dia., 0.31" Max Tie Width, PA66, Black, 1000/pkg

### Product Dimensions

<b>Length L (imperial)</b>	0.86 "
<b>Length L (metric)</b>	21.8 mm
<b>Width W (imperial)</b>	0.61 "
<b>Width W (metric)</b>	15.5 mm
<b>Cable Tie Width Max (imperial)</b>	0.31 "
<b>Cable Tie Width max. (metric)</b>	7.9 mm
<b>Height H (imperial)</b>	0.37 "
<b>Height H (metric)</b>	9.4 mm
<b>Mounting Hole Diameter D (imperial)</b>	0.2 "
<b>Mounting Hole Diameter D (metric)</b>	5.1 mm

### Logistics and Packaging

<b>Quantity per</b>	bag
<b>Package Quantity</b>	1000

### Material and Specifications

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL94 V2
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Conformity</b>	Yes
<b>Certification/Specification</b>	UL

**UL Listed (US and Canada)** No

**UL Recognized (US and Canada)** Yes