

Mini-Lynx GLS

ML GLS 827 B22 15W SLV

0035503

Range features



CE

PRODUCT OVERVIEW

Ordering number	0035503
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	GLS
Lamp finish	FROSTED
Dimmable	No
Cap/Base	B22
Type	GLS
EAN code	5410288355030
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	820
Efficacy (Rated) (lm/w)	54.666666667
Watt (Nominal) (W)	15
Equivalent watt (W)	65
Voltage (V)	220-240

Mini-Lynx GLS

ML GLS 827 B22 15W SLV

0035503

DATA TABLE

General data

Ordering number	0035503
Dry applications use only	Yes
Technology	Compact Fluorescent
Energy saving lamp	Yes
Energy class	A
Average life (Rated) (h)	10000
Average life (Nominal) (h)	10000
Lamp finish	FROSTED
Lamp shape	GLS
Dimmable	No
Cap/Base	B22
Type	GLS
EAN code	5410288355030
E-number SE	8357584
Product name	ML GLS 827 B22 15W SLV
Lamp mercury content (mg)	<2
Starting time (max) (s)	< 1.0 Sec
Warm-up time to 60% of full light (max) (s)	< 100 s
Control gear required	NO
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	30000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25° C, cap-up, Stated lumen output may vary if operated in non-standard position

Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	820
Lumen maintenance at end of nominal life (%)	=60%
Luminous flux (Nominal) (lm)	820

Mini-Lynx GLS

ML GLS 827 B22 15W SLV

0035503

Electrical data

kWh per 1000 hours burning time	15
Efficacy (Rated) (lm/w)	54.666666667
Watt (Rated) (W)	15
Watt (Nominal) (W)	15
Equivalent watt (W)	65
Voltage (V)	220-240
Lamp power factor	> 0.55

Physical data


Lamp Length (mm) - C/L	129
Lamp Diameter (mm) - D	64

Mini-Lynx GLS

ML GLS 827 B22 15W SLV

0035503

TECHNICAL DRAWINGS



ENERGY LABEL

