

Metal tool box with assortment, 129 pieces 1/4 " + 3/8", inch sizes, 1483KHD3RB-FF1



Article number: 1483KHD3RB-FF1

Size: 523x257x300cm

Weight: 11,000 g

Packing quantity: 1pc. "

129-piece Metal tool case with range 1/4 " + 3/8".

- For aircraft mechanics
- Suitable for all major aircraft types
- Especially suitable for maintenance 1/4 ", 3/8"

Lid Compartment – 5 pieces



481-300
Hammer



300mm

3625N-32
Superflex plastic hammer



-

2509
Flexible gripper



300 mm

2535F1
Magnetic lifter



1kg

7762
Extension 3/8 "



250mm

79 Pieces



Open-ended spanner	6Z	7 / 8x15 / 16 ", 1x1.1 / 8", 1.1 / 16-1.1 / 4 "
Ratchet 1/4 ", narrow head	6950SL	-
Drive handle 1/4 "	6956	-
Flexible handle 1/4 "	6958	-
Extension 1/4 "	6960	50 mm
Extension 1/4 "	6961	100 mm
Universal joint 1/4 "	6966	-
Ratchet 3/8 ", narrow head	7750SL	-
Crank 3/8 "	7752	-
Renewals 3/8 "	7760	75, 125 mm
3/8 "to 1/4" transitional part	7764	-
1/4 "to 3/8" transitional part	7765	-
Universal joint 3/8 "	7766	-
Bit holder 1/4 "	6972H	-
Bit holder 3/8 "	7407H	1/4 " - 3/8"
3/8 "to 1/2" transitional part	8164	-
1/2 "to 3/8" transitional part	8165	-
double-6kant shortly	A6700DZ	7/32 ", 1/4", 9/32 ", 5/16", 11/32 ", 3/8", 7/16 ", 1/2"
double-6kant, long	A6800DZ	7/32 ", 1/4", 9/32 ", 5/16"
double-6kant shortly	A7400DM	10, 13 mm
double-6kant shortly	A7400DZ	1/2 ", 9/16", 5/8 ", 11/16", 3/4 "
double-6kant, long	A7402DZ	3/8 ", 7/16", 1/2 ", 9/16"
double-6kant, customs	7800DZ	13/16 ", 7/8", 1 "
Bit set for slotted, Phillips, TORX®, Allen and TORQ-SET® screws 28-piece set	-	-
Joint Sockets 1/4 "	A6710DZ	5/16 ", 3/8", 7/16 "
Ratchet ring spanner	1320RZ	1 / 4x5 / 16 ", 3 / 8x7 / 16 "

13 pieces



Cranked screwdriver for slotted screws, double angulation	2047-1.2-8	1,2x8x150
Offset wrench for Phillips screws, double angulation	2047PR-1-2	PH1 & 2
ERGO Flathead screwdriver	8020L-BE	0,5x3x75
Ergo screwdriver for slotted screws	BE-8155	1,2x6,5x125
Ergo screwdriver for slotted screws, hex shaft and approach	BE-8260	1,6x8,0x175
BE-8611 / BE 8621		
Ergo screwdriver for Phillip screws	BE-8611	PH1x75, PH2x100
Ergo Screwdriver for Phillips screws	BE-8601	PH1x25
M. screwdriver through-blade for slotted screws	9715-14-250	2.5x14x250
Telescopic articulated mirror	5515T-52	Ø 50 mm
Scriber cranked	1177-SCRIBE	230 mm
O-ring Lever	BE-3529	175 mm
Calipers	1150-1 / 2 H / P	150 mm

12 pieces



Ergo side cutter	2101GC	160mm
Needle nose pliers	2421 GC-180IP	180mm
Wire twisting pliers	2855D	282mm
Ergo Water Pump Pliers	8224CIP	-
Tape measure	1162N-half	2m
Driver M. Hand Protection	3658A	2x150, 3x150, 5x150mm
Tachenlampe	62168202	-
Aluminum mandrel	454800500	25x150mm hhw
Tyre tread gauge	431301000	30mm hhw
Tyre tread gauge	431301100	80mm

20 pieces



Flexible handle 1/2 "	8158-1 / 2	380 mm
Open-ended spanner, cranked, customs	1300Z	1 / 4x5 / 16 ", 3 / 8x7 / 16" 1 / 2x9 / 16 ", 19 / 32x11 / 16 ', 5 / 8x3 / 4", 25 / 32x13 / 16 ", 7 / 8x15 / 16"
Open-ended spanner, Liliput	1931Z	7/32 ", 1/4"
Open-ended spanner	6Z	1 / 4x5 / 16 ", 3 / 8x7 / 16" 1 / 2x9 / 16 ", 19 / 32x11 / 16 ', 5 / 8x3 / 4", 25 / 32x13 / 16 "
Ergo Adjustable Wrench 6 ", chromed	9070C	158x20 mm
Double ring wrench	XID1618A	1 / 4x9 / 32 "
Double ring wrench	XID1514A	7 / 32x15 / 64 "
Open-ended spanner	DS2018A	5 / 16x9 / 32 "

