

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

38-00-1337

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 PC Board Connector, Right Angle, with Cat Ear Terminal, 7 Circuits



Series

image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-10-07 \(PDF\)](#)
- [Product Specification PS-99020-0088 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Receptacles

Series

4455

Application

Board-to-Board, Signal

Overview

KK® Interconnect System - Molex

Product Name

KK® 254

UPC

800753732155

Physical

Circuits (Loaded)

7

Circuits (maximum)

7

Color - Resin

Natural (White)

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

No

Material - Metal

Phosphor Bronze

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

0.760/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.30mm

PCB Locator

No

PCB Retention

Yes

PCB Thickness - Recommended

1.60mm

Packaging Type

Tray

Pitch - Mating Interface

2.54mm

Pitch - Termination Interface

2.54mm

Plating min - Mating

1.016µm

Plating min - Termination

1.016µm

Polarized to PCB

Yes

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

2.5A

Grounding to PCB

No

Voltage - Maximum

250V

Solder Process Data

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

4455Series

Mates With

42153 KK® Wire-to-Board Header, 4094
KK® Wire-to-Board Header, 42376 KK®
Header, 42375 KK® Header, 42377 KK®
Header, 42152 KK® Wire-to-Board Header,
4030 KK® Wire-to-Board Header

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235

Material Info

Old Part Number	A-4455-AZ07C(P909)
-----------------	--------------------

Reference - Drawing Numbers

Product Specification	PS-10-07, PS-99020-0088
Sales Drawing	SDA-4455

This document was generated on 01/21/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION