



Datasheet for part number TR1004RMS1NB

Our Catalog Part Number: TR1004RMS1NB
Our Global Manufacturing Part Number: 192926-0440
Brand: Cannon Product Category: Trident Product Line: Trident Series: TR

Product Datasheet	
Series	Trident Ringlock
Operating Voltage	Up to 250 V ac rms Up to 380 Vac rms (Size 1807 only)
Contact Current Rating	Up to 13 A
Operating Temperature	-55°C to +105°C
Insulation Resistance	5000 Megaohms at 500 V dc
Durability	Up to 500 Mating Cycles
Sealing	Up to IP65
Flammability Rating	UL94-V0
Materials and Finishes	Connector Body: Black Nylon Coupling Ring: Nickel Plated Copper Alloy Bayonet Pins: Stainless Steel Bayonet Pins Support Band: Nickel Plated Copper Alloy
Shell Size	10
Number of Contacts	04
Type	Receptacle
Contact Type	Accepts Male Contacts
Mounting Style	Standard
Material	Nylon
Colour	Black