







THREE KINDS OF DIFFERENT POCKETS AS 1 SET
USED FOR 7P ONLY



TYPE "B"




△ PEELING RESISTANCE : 0.196N-0.686N (20gf-70gf)
SPEED : 300mm/min

CUSTOMER DRAWING

TE Connectivity

REV	C2
-----	----



FOR 7P ONLY

THREE KINDS OF DIFFERENT POCKETS AS 1 SET
USED FOR 7P ONLY




Fig-1




Fig-2

△ PEELING RESISTANCE : 0.196N-0.686N (20gf-70gf)
SPEED : 300mm/min

CUSTOMER DRAWING

A3 00779 C-292173

SCALE

SHEET 2 OF 6

REV C2

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

ES

00

P

LTR


DESCRIPTION

DATE


DWN

APVD


LAYOUT FOR 292173-X,1-292173-X



5 POS. & ABOVE POS.




3 POS.



2 POS.

RECOMMENDED P.C. BOARD LAYOUT
(P.C.B THK:0.8mm MIN)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

STE

TE Connectivity

NAME

SMT TYPE POST HDR ASS'Y (H)
WITH BOSS &TAIL TYPE
(TE CT CONN. 2mm PITCH)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-292173

SCALE 5:1

SHEET 4 OF 6

REV C2

