

Classic ECO Ball

CLECO BAL 240V 28W E27 SV1

0023486



Range features

- 1:1 replacement of Incandescent Ball lamp
- More efficient - more savings
- Excellent colour rendering (CRI = 100)
- Instant illumination
- Sparkling light output
- Less heat generation than incandescent lamp
- Less CO2 emissions
- Identical shape as standard incandescent lamp
- Commercial and domestic application
- 100% dimmable
- Average rated life 2000 hrs - up to two times more average life compared to incandescent lamps



PRODUCT OVERVIEW

Light colour	828 Homelight
Technology	Halogen
Ordering number	0023486
Average life (Rated) (h)	2000
Energy class	D
Lamp shape	Ball
Lamp finish	Clear
Dimmable	Yes
Cap/Base	E27
Type	Ball ECO
EAN code	5410288234861
CRI (Ra)	100
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	370
Watt (Nominal) (W)	28
Equivalent watt (W)	37
Voltage (V)	240

Classic ECO Ball

CLECO BAL 240V 28W E27 SV1

0023486

DATA TABLE

General data

Ordering number	0023486
Technology	Halogen
Average life (Nominal) (h)	2000
Average life (Rated) (h)	2000
Energy saving lamp	No
Energy class	D
Lamp shape	Ball
Lamp finish	Clear
Dimmable	Yes
Cap/Base	E27
Type	Ball ECO
EAN code	5410288234861
E-number SE	8355577
E-number FI	4740155
Long description	1:1 replacement of Incandescent Ball lamp. More efficient - more savings. Excellent colour rendering (CRI = 100). Instant illumination. Sparkling light output. Less heat generation than incandescent lamp. Less CO2 emissions. Identical shape as standard incandescent lamp. Commercial and domestic application. 100% dimmable. Average rated life 2000 hrs - up to two times more average life compared to incandescent lamps
Product name	CLECO BAL 240V 28W E27 SV1
Lamp mercury content (mg)	0
Starting time (max) (s)	0.01
Warm-up time to 60% of full light (max) (s)	Instant full light
Control gear required	No
Fixture rating	Open
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-2
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	> 8000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

Classic ECO Ball

CLECO BAL 240V 28W E27 SV1

0023486

Optical data

Light colour	828 Homelight
CRI (Ra)	100
Suitable for accent lighting	No
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	370
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	370

Electrical data

kWh per 1000 hours burning time	28
Watt (Rated) (W)	28
Watt (Nominal) (W)	28
Equivalent watt (W)	37
Voltage (V)	240
Lamp power factor	1

Physical data


Weight (kg)	0.02
Lamp Length (mm) - C/L	74
Max. Lamp Diameter (mm) - D	46
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	7.60 x 4.55 x 4.55
Inner package dimensions (L x W x H) (cm)	23.50 x 10.00 x 8.50
Inner package net weight (kg)	0.18
Outer package dimensions (L x W x H) (cm)	52.00 x 25.50 x 19.00

Classic ECO Ball

CLECO BAL 240V 28W E27 SV1

0023486

TECHNICAL DRAWINGS



ENERGY LABEL

