

- 6101-0002 - HPS-501-G-Range E
- Pressure range - 75 to 374 mBar (30" to 150" H₂O)
- Burst Pressure - 1.4 Bar (550" H₂O)
- Pressure connection - Side entry
- Single pole, Normally open
- Diaphragm material - Urethane
- Operating Temperature +4°C to +65°C
- Electrical rating - 30V 40mA – resistive DC
- Mechanical life - 20,000,000 cycles



Outline Dimensions

