


DESCRIPTION CONTROL			
REV	DESC	DATE	ECN NO



PIN ASSIGNMENT			
P1			P2
1			1
2			2
3			3
4			4
5			5
6			6
7			7
8			8
9			9
10			10
11			11
12			12
13			13
14			14
15			15
16			16
17			17
18			18
19			19
20			20
21			21
22			22
23			23
24			24
C1	RED-IN		C1
C2	GREEN-IN		C2
C3	BLUE-IN		C3
C4			C4
C5	COAX-GND		C5
S	BRAID		S

	*	390	CARTON:46*30*25CM	A/R	PCS
	*	390	PE BAG:30'*28'*0.08MM	A/R	PCS
	*	210	PE BAG:7'*10'*0.06MM	1	PCS
	*		TIE-A-BLACK	100.0	MM
	15	200032000160	TUBE-HT-Ø5.0MM	6.0*2	MM
	14	370	TUBE-HT-Ø2.0MM	20.0*2	MM
	13	240010800005	SRW-RE32/BLACK10	4	PCS
	12	370	HI TEAMP TAPE:W:25MM;	80*2	MM
	11	370	FOIL-CU-30MM	65*2	MM
	10	220	PVC-BLACK10/50	35	G
	9	210	SOL-WIRE-FULL TIN-1.2	3.0	G
	8	200034000034	TUBE-HT-Ø3.0MM (thin)	10.0*8	MM
	7	200034000033	TUBE-HT-Ø2.0MM (thin)	6.0*14	MM
	6	200034000032	TUBE-HT-Ø1.0MM (thin)	15.0*14	MM
	5	200034000032	TUBE-HT-Ø1.0MM (thin)	5.0*6	MM
	4	220	PE-5321	8.5	G
	3	220	SOL-WIRE-FULL TIN-1.0	1.2	G
	2	204-2451101200-C	D.V.I-24+4+KEY-M(BK)	2	PCS
	1	1308241100051	[30#*3COAX(S)+(28#*1P+D+A)*7C+28#*1P+28#*5C]+A+B-BK10-9.5U20276	2.0	M
NO	PART NO.		DESCRIPTION	QTY	UNIT

RoHS COMPLIANT



OUTER MOLDING	AV.DVI-053		
INNER MOLDING	AV.DVI-052		
ITEM: 489333			
DRAWN,BY: 楊燕瑛			REV R
CHECKED,BY:		SCALE:NONE	DATE: 2007/12/27
APP'ED,BY:		CUSTOMER:C331(RS)	PAGE: 1/1
CUSTOMER P/N: 489333			
ALL DIMENSIONS IN mm			