

**CLAMP METERS**

**Perfect fit the palm of your hand**  
**Compact, truly portable and high performance**

**Digital AC/DC Current Mini Clamp Meter**

**NEW**

- 24mm dia tear drop shaped jaws.
- Minimum resolution of 0.01A AC/DC.
- Data hold function.
- Auto zero function to allow one touch zero adjustment.

● Specifications

AC A	40/300A(Autoranging)
DC A	40/300A(Autoranging)
Conductor Size	∅24mm max.
Safety Standard	IEC61010-1 CAT. III 300V IEC61010-2-032
Power Source	1.5V button cell×2 type LR-44 or SR-44
Dimensions	147(L)×59(W)×25(D)mm
Weight	100g approx.



CE

**MODEL 2033**

**AC/DC Digital Clamp Meter, from 0 to 2000A**

**NEW**



**MODEL 2003A**

- Tear drop shaped jaws for ease of use in crowded cable areas and other tight places.
- Auto null function to allow one touch zero adjustment.
- MAX measurement function for easy reading of maximum input over a certain period of time.

### ● Specifications

AC A	400/2000A
AC V	400/750V
DC A	400/2000A
DC V	400/1000V
$\Omega$	400/4000 $\Omega$
Continuity	400 $\Omega$
Output Voltage	400/2000A DC 400mV/200mV
Conductor Size	∅55mm max.
Safety Standard	IEC61010-1 CAT. III 600V IEC61010-1 CAT. II 1000V IEC61010-2-031, IEC61010-2-032
Power Source	R6P(AA) (1.5V) × 2 Approx. 100 hours in continuous use
Dimensions	250(L) × 105(W) × 49(D)mm
Weight	530g approx.