



# ThermaBind T200 Thermal Binder

4400408

## Product Description

Ideal for general office use, the ThermaBind T200 adds a stylish 'perfect bound' look to documents and presentations, binding up to 200 80gsm A4 sheets in a single document or a series of smaller ones simultaneously. Using easy to operate controls, the binding process takes a fixed time of 40 seconds and there is an integral cooling tray for completed work.

## Features

- Binding capacity - up to 200 sheets (80gsm) - Using 20mm covers
- Easy to operate controls; integral cooling tray for completed work; Binding Capacity up to 200 sheets; Fast binding with a fixed cycle time of 40 seconds; Kensington Microsaver slot for security
- Kensington Microsaver slot for security
- Document Support and integral (21mm) cooling tray - Bound documents can be left to cool to avoid confusion with 'work in progress.'
- Simple to operate controls
- Fixed Binding Cycle
- Audio and visual cycle complete signals
- Fast binding with a fixed cycle time of 40 seconds

## Product information

**Gross weight** 0.89kg

## Retail Packaging Information

**Depth** 110mm  
**Width** 475mm  
**Height** 176mm  
**Gross weight** 1.248kg  
**UPC#** 5028252234825  
**Unit quantity** 1

## Master Case Information

**Depth** 240mm  
**Width** 490mm  
**Height** 725mm  
**Gross weight** 10.9kg  
**UPC#** 5028253234824  
**Unit quantity** 8

## Shipping Information

**Country of origin** PT  
**Minimum Order Quantity** 1

## General information

**Colour** Dark Grey