



ENGLISH

Datasheet


Stock No: 712-5395

RS Pro White Hook Up Wire, 0.22mm² CSA, 1000 V 1.4 A 24 AWG, 500m



Cable Construction

Conductor	Tinned Copper
square(mm ²)	0.22
Construction	T0.2±0.008×7
Standard Dia.(mm)	0.60
Insulation	PVC
Thickness	0.3
Insulation Dia.(±0.1mm)	1.20

**Electrical Characteristics**

Max.Conductor DC Resistance at 20 °C (Ω /Km)	<86.2
Min.Insulation DC Resistance at 20 °C (M Ω *Km)	200
Rated Temperature(°C)	85
Rated Voltage (V)	1000