

Cable marker - WMTB (35X15)R - 0817316

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Cable marker, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Assembly with cable binders, Cable diameter: ≥ 6 mm, Lettering field: 35 x 15 mm

Why buy this product

- Made from high-quality polyester foil
- Labeling service: Phoenix Contact can custom-label all conductor markers according to your requirements
- Conductor marking for marking and bundling conductors indoors
- The marker has two fastening eyes so that it can be attached to the conductor by means of PKB ... cable binders

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 125741
Weight per Piece (excluding packing)	659.8 g
Custom tariff number	39191080
Country of origin	Germany

Technical data

Dimensions

Length (b)	48 mm
Width (a)	15 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1700
Number of individual labels per row	2

Cable marker - WMTB (35X15)R - 0817316

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black