




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
GP	00		K3	REVISED PER ECO-11-004835	11MAR11	RK HMR



"AMP", PART NO. & DATE CODE, MARKED IN AREA INDICATED, ON FAR SIDE

- CONNECTOR ACCEPTS SIZE 20 DF PIN CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
- CONNECTOR COMPLIES WITH 108-40005 WHERE APPLICABLE.
- MOLDED PARTS: NYLON, FLAME RETARDANT, 94V-O RATED, GLASS FILLED, BLACK.
- SHELLS: STEEL PER ASTM A109.
- ZINC PLATED PER ASTM B633; TYPE II; CLASS SC1; YELLOW CHROMATE.
- TIN OR TIN-LEAD PLATED OVER COPPER UNDERPLATE.
- CHROME PLATED.
- TIN PLATED OVER COPPER UNDERPLATE.
- ZINC PLATED .000200-.000400 THICK, YELLOW TRIVALENT CHROMIUM CHROMATE COATING.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



10	OBSOLETE	SMALL PACK	9	NO	4—205204—0
		STANDARD	9	NO	205204—9
		STANDARD	8	NO	205204—8
	SUPERSEDED BY 205204—9	SMALL PACK	5	NO	205204—7
		STANDARD	8	YES	205204—4
	SUPERSEDED BY 205204—8	STANDARD	6	NO	205204—3
	OBSOLETE	STANDARD	7	NO	205204—2
	SUPERSEDED BY 205204—9	STANDARD	5	NO	205204—1
		PACKAGING TYPE	SHELL FINISH	GROUNDING INDENTS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 07/19/85	TE Connectivity		
DIMENSIONS: INCHES		CHK J. GERACE 07/29/85			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME PLUG CONNECTOR, SIZE 1, 9 POS., AMPLIMITE HDP		
		PRODUCT SPEC -			
		APPLICATION SPEC -			
MATERIAL SEE NOTES	FINISH SHELLS: SEE TABLE	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-205204
		CUSTOMER DRAWING	SCALE NTS	SHEET 1 of 1	REV K3