

Datasheet

RS Pro Black Self Amalgamating Tape

RS Stock No: **494-691**



Product Details

RS Pro butyl rubber-based self amalgamating tape in black colour, is suitable for insulation, filling voids and irregular shapes in joints. The tape measures 38 mm x 10 m. This tape provides moisture-proof seals on telecommunication cables, insulation and cable sheaths, joints and terminations and for split bolt connections.

Features and Benefits

- Butyl rubber-based self amalgamating tape
- Excellent conformability, easily compressed and moulded by hand
- Will not corrode copper
- Dielectric strength: 16 kV/mm
- Measures 38 mm x 10 m

**Specifications:**

| | |
|-------------------------------|---|
| Application | Telecommunications, Insulation & Cable Sheath, Joints & Terminations, Split Bolt Connection |
| Backing Material | Butyl Rubber |
| Colour | Black |
| Breakdown Voltage | 32000 V |
| Length | 5 m |
| Maximum Operating Temperature | +80°C |
| Minimum Operating Temperature | -30°C |
| Tensile Strength | 4.5 N/cm |
| Thickness | 2 mm |
| Width | 38 mm |
| Operating Temperature Range | -30 to +80°C |