

Specifications for PermaSleeve Wire Marker Sleeves for the IDXPERT Printer

Article No.	800805
Brady Material No.	B-342
Material Type	Heat-shrink Polyolefin Sleeve
Colour	Yellow
Finish	Matt
Order Reference	XPS-125-CONT-YL-BK
Printer Compatibility	IDXPERT
Size - Length (m)	3.65
Size - Width (mm)	5.96
Additional Information	Heat-shrinkable;Self-Extinguishing
Total Qty per Pack	1 Sleeve(s) / Roll
Wire Gauge	22-16
Approval/Compliance	SAE-AMS-DTL-23053/5 C (Class 1); SAE-AS-81531; MIL-STD-202 method 215K; UL224
Ribbon Series	R4300
Application	Wire & Cable Marking
Industry	Data & Telecommunications;Electrical
Description	PermaSleeve™ Heat Shrinkable Wire Marker Sleeves for the IDXPERT™ printer
Max. Service Temp. °C	130
Max. Wire/Cable Diameter (mm)	2.80
Min. Service Temp. °C	-70
Min. Wire/Cable Diameter (mm)	1.20
Printable Sides	Single-sided Printable
Shape	Continuous
Shrink Ratio	3:1