



fitted with

- work equipment**
- connected load**
- power consumption**
- glare-free**
- system of protection**
- class of protection**
- usage**
- luminaire body**
- lamp cover**
- weight (net)**
- mains lead**
- fastening**
- dimension**
- special features**

- 24 x Light-emitting diode
- light colour daylight white, 5300-6400 K
- Energy efficiency category A+
- without
- 22-29 V; DC
- approx. 15 W
- without
- IP 67
- III
- without switch
- aluminium/plastic, anodised, aluminium coloured anodised
- acrylic clear
- approx. 0.7 kg
- approx. 3.0 m; with free stranded wires
- screws
- A=616mm, C=570mm
- direction of beam +/- 45° adjustable

illuminance

measuring conditions: d=50cm

Em: 360 lx
Emax: 699 lx
Emin: 125 lx

