

Transition sleeve from hose to cable - WP-EC TPE HF 34,5 BK - 3240979

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




End sleeves, transition sleeves, from hose to cable

Image shows WP-EC TPE HF 10.0 BK version



Key commercial data

Packing unit	25 pc
Minimum order quantity	25 pc
GTIN	 4 046356 710978
Weight per Piece (excluding packing)	9.37 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	44.2 mm
Inner diameter (f)	29.00 mm
Outside diameter	34.50 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Short-term temperature	150 °C

General

Color	black
Components	Halogen-free
Inflammability class according to UL 94	HB

Transition sleeve from hose to cable - WP-EC TPE HF 34,5 BK - 3240979

Technical data

General

Material	TPE
----------	-----

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002584
ETIM 5.0	EC002584

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

UL Recognized


Ex Approvals

Approvals submitted

Approval details

Transition sleeve from hose to cable - WP-EC TPE HF 34,5 BK - 3240979

Approvals

UL Recognized 

Phoenix Contact 2015 © - all rights reserved
<http://www.phoenixcontact.com>