




M-6565 3



CORD GUARD
SHOWN IN
EXTENDED
POSITION



CORD ACCOMMODATION

NORTH AMERICAN
16/3 SJ - 12/3 SJ (.325 - .475 DIA.)

INTERNATIONAL (HAR CORD)
3X1.5 mm² - 3-2.5 mm² (8MM-12mm DIA.)

CAT. NO H320C

TITLE

20/16A 250V A.C. THREE - WIRE
I.E.C. STRAIGHT BLADE VALISE
CONNECTOR

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOUSING	NYLON	BLACK
CONTACT SPRING	BRASS	
WIRE CLAMPING NUT	STEEL	NICKEL PL.
BINDING SCREW	STAIN. STEEL	BLACK
GR. BINDING SCREW	STAIN. STEEL	GREEN
CORD CLAMP SCREW	STEEL	ZINC PL.
CORD GUARD	RUBBER	BLACK

3	.787 WAS 7.87 PER DCN 19209 SPN	DJP	11/29/12
2	.787 MIN WAS .813 +/- .015. ALL OTHER DIMS REVISED 3 DECIMAL PLACES TO TWO. PER DCN 18611 SPN	DJP	1-30-12
1	CONVERTED ALL DIMS TO 3 PL DECIMAL & TOL ADDED PER DCN #7773 AMZ DB		7-10-00

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE.

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE DIVISION HARVEY HUBBELL, INC. BRIDGEPORT, CONN.	
FRACTIONS	± 1/64	DR. BY <u>ALL</u>	APP. BY
DECIMALS	± .005	TR. BY	SCALE <u>FULL</u>
ANGLES	± 2°	CHK'D. BY	DATE <u>6-7-87</u>

CODE 74545

DIMENSION SHEET FOR CAT. NO. H320C

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-6565

3