



Product Information

ETX085x60-Ø12 NL65-Type A

EAN 4031582330830

Wheel centre made of steel, tread made of Polyurethane, casted, precision ball bearing, sealed

Wheel diameter	85 mm
Width of Tread	60 mm
Axle Hole Ø	12 mm
Hub length	65 mm
Temperature	- 20 / + 60 °C
Dynamic Load capacity	600 kg
Static Load capacity	1200 kg
Hardness of tread	A 92 Shore

