

MOSA M12 FEMALE 0° FIELD-WIREABLE (IDC)

D-cod., 4-pol., 0,25-0,34mm², shielded

Female M12, straight
Field-wireable (IDC terminals)
D-coded, 4-pole, shielded, CAT 5

[Link to Product](#)

Illustration



Product may differ from Image

Technical Data

Operating voltage	max. 50 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.14...0.34 mm ² (AWG 26...22)
Sealing range (cable diameter)	4.5...8.8 mm
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

General data

Temperature range	-40...+85 °C
-------------------	--------------

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1