



ENGLISH

Datasheet

Stock No: 413-9130

# RS Pro PUR 5000mm Long transparent Flexible Ducting Reinforced, 16mm Bend Radius



## Product Details

### Flexible Ducting (Copper plated helix)

An RS Pro brand of polyurethane (PU) hosing with copper-plated steel spiral. Designed to be self-extinguishing and can be used for suction and the transport of dusts, chips and abrasive material.

Copper plated spring-steel helix between two layers of crystal clear polyurethane  
Highly flexible with excellent internal and external abrasion resistance

May also be used in foundry, general industrial and agricultural applications

Temperature range -40 to +90°C

### Note

All data refers to performance at 18°C. Any changes in temperature will affect the performance data



## Specifications

Inner Diameter	63mm
Outer Diameter	63.8mm
Material	PUR
Length	5000mm
Suitable Applications	Abrasive Material, Chemical, Dust, Granule, Saw Dust
Colour	Transparent
Bend Radius	16mm
Reinforced	Yes