
Item no.: 2002-3207
Product description: Triple deck terminal block 6-conductor earth PE without marker carrier housing color: green-yellow internal commoning suitable for Ex e applications



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Number of levels	3
Cross section [mm ²]	0.25 - 2.5 mm ²
Cross section [AWG]	22 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm ²]	0.25 - 4 mm ²
Cross section [AWG]	22 - 12 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®S Connection
Weight	20.5 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	6
No. of potentials	1
Height	69.5 mm
Height	2.736 in
Width	5.2 mm

Width	0.205 in
Depth	93.5 mm
Depth	3.681 in
Strip length from	10 mm
Strip length to	12 mm



Strip length	0.43 in
Customs Tariff No.	85369010
Country of Origin	Deutschland
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
2002-3207	CCA	NL6387			0,2-2,5/4
2002-3207	CSA	154112-1536069			22-12
2002-3207	GL	6187-05HH			4,0
2002-3207	KEMA	NL2116586.02			0,2-4
2002-3207	LR	91/20112(E6)			4,0
2002-3207	PTB	IECExPTB03.0004U			0,2-4
2002-3207	PTB	PTB03Atex1162U			0,2-4
2002-3207	RosTest	8189158			0,2-4
2002-3207	UR	E45172			22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected