


NOTES:

- 1
- CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1,27 CENTERS .
FOR CABLE REQUIREMENTS SEE AMP APPLICATION SPECIFICATION 114-19022.
- 2
- THESE RECEPTACLE CONNECTORS MATE WITH 0,64^{±0,05} mm SQUARE OR ROUND POSTS
ON 2,54mm GRID.
- 3
- MARK INDICATING FIRST CABLE POSITION REFERRING TO CONTACT POSITION.
- 4
- THERE IS NO POLARIZATION-SLOT AT THIS END IN 6, 10 AND 14 POS CONNECTORS.
- 5
- THESE CONNECTORS CAN BE USED IN CONJUNCTION WITH STRAIN-RELIEF COVERS
OF PARTNR: 100103.
- 6
- THERE IS NO POLARIZATION-SLOT AT THIS END IN 6 POS CONNECTORS.
- 7
- PRODUCT SPECIFICATION 108-19033.
- 8
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



1000	85,9	64	32	6-215915-4	D
1000	80,8	60	30	6-215915-0	D
1000	68,1	50	25	5-215915-0	D
1500	60,5	44	22	4-215915-4	D
1500	55,4	40	20	4-215915-0	D
1500	47,8	34	17	3-215915-4	D
1500	42,7	30	15	3-215915-0	D
1500	37,6	26	13	2-215915-6	D
1500	30,0	20	10	2-215915-0	D
1500	24,9	16	8	1-215915-6	D
1500	22,4	14	7	1-215915-4	D
1500	17,3	10	5	1-215915-0	D
OBSOLETE	1500	14,8	8	0-215915-8	B
1500	12,2	6	3	0-215915-6	D
OBSOLETE	1500	9,7	4	0-215915-4	B
QUANTITY PER REEL	DIM."C"	"B" CABLE POS.	"A" DUAL POS.	PARTNUMBER	PART REV.

±0,1 6,05 +0.1 -0.3 7,3				③ RECEPTACLE CONTACT		PHOSPHORBRONZE Cu Sn6		AT CONTACT-PLACE: 0,8μ GOLD AT WIRING END: 2,5μ TIN ENTIRE UNDERCOATING: 1,27μ NICKEL			
				② COVER		THERMOPLASTIC POLYESTER GF UL 94 -V0		GREY RAL 7032 ONLY FOR REF.			
				① HOUSING							
				COMPONENT NAME		MATERIAL		PLATING / COLOUR			
D6	ECO-09-020935			KK	AEG	31AUG09	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED				
D5	ECR06-29576			A.V.	R.M.	15-12-06	© COPYRIGHT 19 - BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.				
D4	ET00-0243-04			A.V.	R.M.	21-03-05	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION _____,19_____				
D3	ET00-0159-04			A.V.	R.M.	13-07-04	tyco Electronics AMP ITALIA S.p.A Corso F.LLI Cervi, 15 COLLEGNO (TORINO)				
D2	ET00-0180-03			A.V.	R.M.	19-01-04					
D1	ET00-0093-03			SS	-	23-05-03					
D	H-7482			JvL	RV	29-10-92	NAME AMP-LATCH MIL-TYPE RECEPT. CONN. ASS'Y 14,9 PRE-ASSEMBLED 0.8 μM TAPE MOUNTED ON REEL. ④				
LTR.	REVISION RECORD			DR.	CHK.	DATE					
DR.: R.HOGEVEEN		CHK.: R.VERSTIJNEN		APP.: L.V.SOEST		DWG.No.			SIZE	SHEET	REV.LTR.
DATE: 02-02-88		DATE: 03-02-88		DATE: 03-02-88		C-215915			A3	1 OF 1	D6