

Professionally approved products.

Datasheet

2 Port VGA Video Splitter

RS Stock number [745-6712](#)



Description:

Duplicates VGA video signals to two video outputs
 Applications: multimedia, presentations, demos, etc.
 Video bandwidth: 250 MHz
 Supports DDC and DDC2 on Port 1
 Video input: 1x HD15 M, Video output: 2x HD15 F
 Power supply over integrated USB Type A cable
 Cascadable

Specifications:

Device Type:	Splitter
Maximum Resolution:	2560 x 2048 pixels
Number of Ports:	2
Video Connection Type:	VGA