

# Specifications for BMP41/BMP51/BMP53 Labelmaker Labels

<b>Adhesive</b>	Repositionable Rubber
<b>Application</b>	Wire & Cable Marking
<b>Approval/Compliance</b>	UL Recognised
<b>Article No.</b>	143331
<b>Brady Material No.</b>	<a href="#">B-498</a>
<b>Material Type</b>	Vinyl Cloth
<b>Brand</b>	CleanLift™ Series
<b>Colour</b>	Black on White
<b>Environment</b>	Freezer
<b>Finish</b>	Semi-gloss
<b>Description</b>	Repositionable vinyl cloth label for wire, cable and component marking. Adhesive and cloth backing offers excellent holding power, while easily being repositioned and removed. Please Note: This material is UL recognized with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.
<b>Max. Service Temp. °C</b>	80
<b>Max. Wire/Cable Diameter (mm)</b>	2.80
<b>Order Reference</b>	M-7-498
<b>Printer Compatibility</b>	BMP41; BMP51; BMP53
<b>Shape</b>	Square
<b>Size - Height (mm)</b>	12.70
<b>Size - Width (mm)</b>	12.70
<b>Additional Information</b>	Repositionable
<b>Total Qty per Pack</b>	240 Label(s) / Box
<b>Wire Gauge</b>	22-16
<b>Industry</b>	Data & Telecommunications; Electrical
<b>Min. Service Temp. °C</b>	-40
<b>Thickness (mm)</b>	0.185