

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

LOC

DIST

REVISIONS

ES

00

P

LTR

DESCRIPTION

DATE

DWN

APVD


A1

REVISED PER ECO-11-005033



24MAR11

RK


HMR




2 POSITION



SECT A-A




TRADE MARK




VIEW B

GATING RECESS




MATING SECTION




CIRCUIT No.1

CAVITY MARK

KINKING FORMING
BOTH SIDE EACH 2 PLACES
TOTAL: 4 PLACES

VIEW B




NOTES:

1.MATERIAL:
HOUSING:NYLON(G.F.) UL94V-0,COLOR:GRAY,BLUE
POST:PRE-TIN 0.5mm SQ. BRASS WIRETOLERANCES UNLESS
OTHERWISE SPECIFIED:10 ≥ * : ±0.2
30 ≥ * >10 : ±0.25
100 ≥ * >30 : ±0.3
ANGLE : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



MATERIAL

SEE NOTE 1

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

SEE NOTE 1

DWN
S.YAO

06DEC02

CHK
T.SASAKI

31JAN03

APVD
T. SASAKI

31JAN03

PRODUCT SPEC

108-60018

APPLICATION SPEC

114-5223

WEIGHT

SEE TABLE

CUSTOMER DRAWING

STE

TE Connectivity

NAME

AMP Mini CT Connector 1.5mm Pitch

Single Row HDR Ass'y (H) DIP Staggered Type with Kink

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-292206


SCALE NON

SHEET 1 OF 2

REV A1

LOC ES	DIST 00	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

0.23	2.5	7.0	5.1	3.0	3		9-292206-3
1.11	3.0	32.5	30.6	28.5	20	7-292206-0	2-292206-0
1.06	3.0	31.0	29.1	27.0	19	6-292206-9	1-292206-9
1.01	3.0	29.5	27.6	25.5	18	6-292206-8	1-292206-8
0.96	3.0	28.0	26.1	24.0	17	6-292206-7	1-292206-7
0.91	3.0	26.5	24.6	22.5	16	6-292206-6	1-292206-6
0.86	3.0	25.0	23.1	21.0	15	6-292206-5	1-292206-5
0.81	3.0	23.5	21.6	19.5	14	6-292206-4	1-292206-4
0.75	3.0	22.0	20.1	18.0	13	6-292206-3	1-292206-3
0.70	3.0	20.5	18.6	16.5	12	6-292206-2	1-292206-2
0.65	3.0	19.0	17.1	15.0	11	6-292206-1	1-292206-1
0.60	3.0	17.5	15.6	13.5	10	6-292206-0	1-292206-0
0.54	3.0	16.0	14.1	12.0	9	5-292206-9	292206-9
0.49	3.0	14.5	12.6	10.5	8	5-292206-8	292206-8
0.44	3.0	13.0	11.1	9.0	7	5-292206-7	292206-7
0.40	3.0	11.5	9.6	7.5	6	5-292206-6	292206-6
0.34	3.0	10.0	8.1	6.0	5	5-292206-5	292206-5
0.29	3.0	8.5	6.6	4.5	4	5-292206-4	292206-4
0.24	3.0	7.0	5.1	3.0	3	5-292206-3	292206-3
0.19	3.0	5.5	3.6	1.5	2	5-292206-2	292206-2
WEIGHT (g)	D	C	B	A	Pos.	BLUE	GRAY
DIMENSIONS					PART NO		

DIMENSIONS: mm	DWN -	MATERIAL -	FINISH -
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK -	 TE Connectivity	
0 PLC ± -	APVD -		
1 PLC ± SEE SHEET	PRODUCT SPEC -		
2 PLC ± 1 OF 2	APPLICATION SPEC -	NAME AMP Mini CT Connector 1.5mm Pitch Single Row Post HDR Ass'y (H) DIP Staggered Type with Kink	
3 PLC ± -	WEIGHT -	SIZE A4	CAGE CODE 00779
4 PLC ± -		DRAWING NO C-292206	
ANGLES ± -		RESTRICTED TO -	
	CUSTOMER DRAWING		
	SCALE -	SHEET 2 OF 2	REV A1