

# Zarges Industrial Platform Steps



High strength stepladder, ideal for regular use

- Tested and certified to both BS 2037 Class 1 and EN 131
- Patented 7-point connection between tread and stile with reinforcing support rod through the centre of the tread.
- Non-slip, replaceable rubber feet provide firm footing
- Stand safely on large serrated treads (84 mm deep)
- Smooth 'box section' stiles that are comfortable to hold - no sharp edges
- Optimal stability thanks to locking side bars on both sides
- Large checker surface platform (31.7 cm x 25.3 cm) - with knee rail for safe and comfortable work at height.
- Knee-rail: approx. 60 cm above the platform

Product Code	No. of Treads	Closed Length (m)	Platform Height (m)	Base Width (m)	Base Spread (m)	Stile Dimension: front / back (mm)	Weight (kg)
49678 RS: 7990691	8	2.47	1.70	0.53	1.41	87 x 20 / 40 x 20	9.78
49680 RS: 7990694	10	2.93	2.13	0.57	1.69	87 x 20 / 55 x 20	11.63
49682 RS: 7990698	12	3.39	2.56	0.62	1.98	87 x 20 / 55 x 20	13.55