

Datasheet

RS Pro SafetySure 13A, BS Standard fixing, Passive, 2 Gang RCD Socket, Metal Clad, Surface Mount No, 230 V ac, Grey

RS Stock No: **687-7320**



Product Details

RS Pro 2-gang RCD socket in grey colour, has a voltage rating of 230 V ac and current rating of 13 A. This switched RCD socket is made from MetalClad for durability. This BS standard fixing socket is surface mountable.

Features and Benefits

- Current rating 13 A
- Voltage rating 230 V ac
- Surface mount technology

**Specifications:**

Colour Family	Grey
Colour	Grey
Current Rating	13 A
Dimensions (L x W x D)	147 x 86.5 x 50 mm
Earth Terminal	Yes
Faceplate Depth	12 mm
Faceplate Mounting Type	Screwed
Finish	Gloss
Fixing Standard	BS Standard
Height	86.5 mm
Minimum Box Depth	50 mm
Mounting Style	Surface Mount
Number of Gangs	2
Number of Poles	2
RCD Type	Passive
Socket Type	BS 1363, BS 7288
Switch Style	N/A
Switch Type	N/A
Switched	No
Trip Current	30 mA
Trip Speed	30 ms
Voltage Rating	230 V ac
Voltage Rating	230 V ac
Width	147 mm