

PTRO-0530 - PTRO

General Part Information

| | | |
|-----------------------------|-------------------|-----------|
| Product Description | | PTRO-0530 |
| Article Number | | 32985 |
| POPNut Type | i | PTRO |
| Standard Bulk Pack Quantity | | 8,000 |

Geometry / Dimensions

| | | |
|---------------------------|-------------------|--------------|
| Thread Size | | M5 |
| Body Type (open / closed) | i | Open |
| Body Features | i | Round |
| Body Length (mm) | | 11.80 |
| Min. Grip Thickness (mm) | | 0.50 |
| Max. Grip Thickness (mm) | | 3.00 |
| Head Style | i | Reduced Head |
| Hole Diameter (mm) | | 7.00 |
| Head Diameter (mm) | | 7.80 |
| Head Thickness (mm) | | 0.80 |
| Barrel Diameter (mm) | | 6.90 |

Material / Weight

| | | |
|--------------------------|-------------------|---------------------|
| Material | i | Stainless Steel 302 |
| Weight per thousand (kg) | | 1.5 |

