

## Fuse plug - P-FU 5X20 LED 60-5 - 3209251

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse plug with LED for 30 - 60 V AC/DC, 0.36 - 0.95 mA, width 5.2 mm, color black

### Why buy this product

- Large-surface labeling option
- Test contacts on both sides of the fuse
- Versions with bipolar defect indicator
- Can be used for overload/short-circuit protection



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 548359
Weight per Piece (excluding packing)	5.28 g
Custom tariff number	85369085
Country of origin	China

### Technical data

#### General

Note	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
Color	black
Insulating material	PA
Inflammability class according to UL 94	V0

#### Dimensions

Width	5.2 mm
Length	23.5 mm

#### General

Fuse	G / 5 x 20
------	------------

# Fuse plug - P-FU 5X20 LED 60-5 - 3209251

## Technical data

### General

Current	6.3 A
Nominal current $I_N$	0.95 mA
Nominal voltage $U_N$	60 V (if used as disconnect terminal block. With fuse, the voltage is determined by the light indicator used.)
	60 V (if used as fuse terminal block)

## Classifications

### eCl@ss

eCl@ss 4.0	27142001
eCl@ss 4.1	27142001
eCl@ss 5.0	27142001
eCl@ss 5.1	27142001
eCl@ss 6.0	27141149
eCl@ss 7.0	27141149
eCl@ss 8.0	27141149

### ETIM

ETIM 4.0	EC002018
ETIM 5.0	EC002018

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / CSA / cULus Recognized

---

#### Ex Approvals

---


#### Approvals submitted


---


## Fuse plug - P-FU 5X20 LED 60-5 - 3209251


### Approvals

#### Approval details

UL Recognized 	
Nominal current I <sub>N</sub>	10 A
Nominal voltage U <sub>N</sub>	60 V

cUL Recognized 	
Nominal current I <sub>N</sub>	10 A
Nominal voltage U <sub>N</sub>	60 V


CSA 	
Nominal current I <sub>N</sub>	10 A
Nominal voltage U <sub>N</sub>	60 V

cULus Recognized 	
------------------------------------------------------------------------------------------------------	--


### Drawings

# Fuse plug - P-FU 5X20 LED 60-5 - 3209251

Application drawing




Application drawing



Fuse terminal blocks in interconnected arrangement, block consisting of 5 fuse terminal blocks

## Fuse plug - P-FU 5X20 LED 60-5 - 3209251

Application drawing



Fuse terminal block in single arrangement,  
block consisting of one fuse terminal block and 4 feed-through terminal blocks